



DENT BRAKE CONVERSION to TECNO



DENT 2 SPOT CALIPER FITTED TECNO KART



BRAKE CONVERSION TO FIT DENT 2 SPOT CALIPER TO EARLY TECNO KARTS TO REPLACE THE ORIGINAL TECNO BRAKE CALIPER



MOUNTING SPECS ARE IN THE BELOW ORIGINAL DRAWING FROM DENT ENGINEERING

WHERE THE PAD RETAINING BOLTS AND SPRINGS MAY MOUNT TOO CLOSE TO THE ORIGINAL BRACKET AND YOU MAY HAVE TO RELIEVE THE BRACKET AROUND THE SPRING TO GIVE SOME CLEARANCE

MOUNTING SPACING ORIGINALLY IS 80MM C/C

THE NEW DENT CALIPER SPACING IS 80MM C/C WHICH THERE IS ENOUGH CLEARANCE ON ORIGINAL MOUNT HOLES TO BE ABLE TO FIT THE NEW DENT CALIPER

